

# TOP FIT™ Bands



TOP FIT™ molar bands anatomically conform to the individual tooth which guarantees a perfect fit on the tooth.

Permanent laser markings on the mesial surface clearly identifies the size and quadrant.

Highly polished outer surface for optimal oral hygiene.

Excellent bond strength through micro etching of the internal band.

Special rolled edges create a perfect edge closure.

A buccal/cusp indent eliminates occlusal interference.


## PRE-WELD Services

Available Loose or Prewelded


adenta offers standard or custom pre-welding services to meet all your practice needs. All pre-weld orders are welded in the standard position unless requested otherwise.

### Labial

Bracket to Bicuspid



Upper Bicuspid: Centered




Lower 1<sup>st</sup> Bicuspid: Centered




Lower 2<sup>nd</sup> Bicuspid: Offset to Occlusal

Buccal Tube to Upper Molar



Upper Molar: Entrance to buccal tube will bisect the mesial/ buccal cusp

Buccal Tube to Lower Molar



Lower Molar: Entrance to buccal tube will bisect the mesial/ buccal cusp

### Lingual Attachments

Lower Molar

Gingival



Occlusal




Button: Bisect the mesiolingual cusp

Gingival



Occlusal




Cleat: Centered

Upper Molar

Gingival



Occlusal




Button: Centered

Gingival



Occlusal



Cleat: Centered

## TOP FIT™ Bands sizes and order info

adenta has taken the guess work out of ordering a band kit. Each band kit includes left and right molar bands graduated in even, closely spaced increments. Choose from three kit assortments:

### Sample Kit

80 Total Bands  
40 Lefts and 40 Rights  
Sizes 32 - 39

### Starter Kit

150 Total Bands  
75 Lefts and 75 Rights  
Sizes 29½ - 44

### Office Kit

300 Total Bands  
150 Lefts and 150 Rights  
Sizes 29½ - 44

### Individual TOP FIT™ Molar Bands

Size	1. & 2. UPPER Molar		1. LOWER Molar		2. LOWER Molar	
	Left/UL	Right/UR	Left/LL	Right/LR	Left/LL	Right/LR
29.5	TF10-UL-295	TF10-UR-295	TF10-LL-295	TF10-LR-295	TF11-LL-295	TF11-LR-295
30	TF10-UL-300	TF10-UR-300	TF10-LL-300	TF10-LR-300	TF11-LL-300	TF11-LR-300
30.5	TF10-UL-305	TF10-UR-305	TF10-LL-305	TF10-LR-305	TF11-LL-305	TF11-LR-305
31	TF10-UL-310	TF10-UR-310	TF10-LL-310	TF10-LR-310	TF11-LL-310	TF11-LR-310
35.5	TF10-UL-315	TF10-UR-315	TF10-LL-315	TF10-LR-315	TF11-LL-315	TF11-LR-315
32	TF10-UL-320	TF10-UR-320	TF10-LL-320	TF10-LR-320	TF11-LL-320	TF11-LR-320
32.5	TF10-UL-325	TF10-UR-325	TF10-LL-325	TF10-LR-325	TF11-LL-325	TF11-LR-325
33	TF10-UL-330	TF10-UR-330	TF10-LL-330	TF10-LR-330	TF11-LL-330	TF11-LR-330
33.5	TF10-UL-335	TF10-UR-335	TF10-LL-335	TF10-LR-335	TF11-LL-335	TF11-LR-335
34	TF10-UL-340	TF10-UR-340	TF10-LL-340	TF10-LR-340	TF11-LL-340	TF11-LR-340
34.5	TF10-UL-345	TF10-UR-345	TF10-LL-345	TF10-LR-345	TF11-LL-345	TF11-LR-345
35	TF10-UL-350	TF10-UR-350	TF10-LL-350	TF10-LR-350	TF11-LL-350	TF11-LR-350
35.5	TF10-UL-355	TF10-UR-355	TF10-LL-355	TF10-LR-355	TF11-LL-355	TF11-LR-355
36	TF10-UL-360	TF10-UR-360	TF10-LL-360	TF10-LR-360	TF11-LL-360	TF11-LR-360
36.5	TF10-UL-365	TF10-UR-365	TF10-LL-365	TF10-LR-365	TF11-LL-365	TF11-LR-365
37	TF10-UL-370	TF10-UR-370	TF10-LL-370	TF10-LR-370	TF11-LL-370	TF11-LR-370
37.5	TF10-UL-375	TF10-UR-375	TF10-LL-375	TF10-LR-375	TF11-LL-375	TF11-LR-375
38	TF10-UL-380	TF10-UR-380	TF10-LL-380	TF10-LR-380	TF11-LL-380	TF11-LR-380
38.5	TF10-UL-385	TF10-UR-385	TF10-LL-385	TF10-LR-385	TF11-LL-385	TF11-LR-385
39	TF10-UL-390	TF10-UR-390	TF10-LL-390	TF10-LR-390	TF11-LL-390	TF11-LR-390
39.5	TF10-UL-395	TF10-UR-395	TF10-LL-395	TF10-LR-395	TF11-LL-395	TF11-LR-395
40	TF10-UL-400	TF10-UR-400	TF10-LL-400	TF10-LR-400	TF11-LL-400	TF11-LR-400
40.5	TF10-UL-405	TF10-UR-405	TF10-LL-405	TF10-LR-405	TF11-LL-405	TF11-LR-405
41	TF10-UL-410	TF10-UR-410	TF10-LL-410	TF10-LR-410	TF11-LL-410	TF11-LR-410
41.5	TF10-UL-415	TF10-UR-415	TF10-LL-415	TF10-LR-415	TF11-LL-415	TF11-LR-415
42	TF10-UL-420	TF10-UR-420	TF10-LL-420	TF10-LR-420	TF11-LL-420	TF11-LR-420
42.5	TF10-UL-425	TF10-UR-425	TF10-LL-425	TF10-LR-425	-	-
43	TF10-UL-430	TF10-UR-430	TF10-LL-430	TF10-LR-430	-	-
43.5	TF10-UL-435	TF10-UR-435	TF10-LL-435	TF10-LR-435	-	-
44	TF10-UL-440	TF10-UR-440	TF10-LL-440	TF10-LR-440	-	-

# TOP FIT™ Bands sizes and order info

Choose from three kit assortments:

- Sample Kit – containing 80 bands
- Starter Kit – containing 150 bands
- Office Kit – containing 300 bands

Kit quantities include half left and half right.



## Maxillary 1<sup>st</sup> & 2<sup>nd</sup> Molar Bands

Item# / Size	29½	30	30½	31	31½	32	32½	33	33½	34	34½	35	35½	36	36½	37	37½	38	38½	39	39½	40	40½	41	41½	42	42½	43	43½	44
TF10-UP-SAMPLE (80)	–	–	–	–	–	2	2	4	4	4	6	6	10	10	10	6	6	4	4	2	–	–	–	–	–	–	–	–	–	–
TF10-UP-STARTER (150)	2	2	2	2	2	2	4	4	6	8	10	10	10	10	12	12	10	8	6	4	4	4	2	2	2	2	2	2	2	2
TF10-UP-OFFICE (300)	4	4	4	4	4	4	8	8	12	16	20	20	20	20	24	24	20	16	12	8	8	8	4	4	4	4	4	4	4	4



## Mandibular 1<sup>st</sup> Molar Bands

Item# / Size	29½	30	30½	31	31½	32	32½	33	33½	34	34½	35	35½	36	36½	37	37½	38	38½	39	39½	40	40½	41	41½	42	42½	43	43½	44
TF10-LO-SAMPLE (80)	–	–	–	–	–	2	2	4	4	4	6	6	10	10	10	6	6	4	4	2	–	–	–	–	–	–	–	–	–	–
TF10-LO-STARTER (150)	2	2	2	2	2	2	4	4	6	8	10	10	10	10	12	12	10	8	6	4	4	4	2	2	2	2	2	2	2	2
TF10-LO-OFFICE (300)	4	4	4	4	4	4	8	8	12	16	20	20	20	20	24	24	20	16	12	8	8	8	4	4	4	4	4	4	4	4



## Mandibular 2<sup>nd</sup> Molar Bands

Item# / Size	29½	30	30½	31	31½	32	32½	33	33½	34	34½	35	35½	36	36½	37	37½	38	38½	39	39½	40	40½	41	41½	42	42½	43	43½	44
TF11-LO-SAMPLE (80)	–	–	–	–	–	2	2	4	4	4	6	6	10	10	10	6	6	4	4	2	–	–	–	–	–	–	–	–	–	–
TF11-LO-STARTER (150)	2	2	2	2	2	2	4	4	6	8	10	10	10	10	12	12	10	8	6	4	4	4	2	2	2	2	2	2	2	2
TF11-LO-OFFICE (300)	4	4	4	4	4	4	8	8	12	16	20	20	20	20	24	24	20	16	12	8	8	8	4	4	4	4	4	4	4	4



**Plastic Band Organizer with Lid**  
 adenta's plastic band organizers are designed for proper band storage and will fit most band cabinets.



**Stackable Band Organizer**

- Modular interlocking design
- Constructed with high quality durable plastic
- Accommodates our plastic band organizer (ordered separately)

### TOP FIT™

Plastic Band Organizer

VMT-BANDS

### TOP FIT™

Stackable Band Organizer

VMT-SBO

## FREE! Prewelding Service for TOP FIT™ Bands and Buccal Tubes

adenta offers complimentary welding for all our bands and buccal tubes. Your weld specifications are kept on file in an effort to streamline the reordering process. In an effort to make this procedure as simple as possible we can also provide you with a band and buccal tube order form.

Competitive Upgrade Chart																																				
1. & 2. UPPER Molar					1. LOWER Molar					2. LOWER Molar																										
adenta	American Contoured	Dentaurum Dentaform	GAC	Lancer Supra	Ormco Mark II	Ormco Original	Ormco Ultima	Ormco Washbon	Rocky Mt. Univ.	TP	Unitek Contoured	Ortho Organizers	adenta	American Contoured	Dentaurum Dentaform	GAC	Lancer Supra	Ormco	Ormco Original	TP	Unitek Contoured	adenta	American Contoured	Dentaurum Dentaform	GAC	Lancer Supra	Ormco	Ormco Original	TP	Unitek Contoured						
			1						2																									28		
		1													2	1												2						28.5		
		2	2								29	29			3												3	29.5		29.5				29		
29.5		3		29.5	1	1					29.5	29.5	29.5		4																					
		3						1							2			1																		
		4			2	2			3.5				30		5																					
30				30	3	3		2	4		30	30	30.5		3		1	2		1	3															
30.5		5	4	30.5							30.5	30.5			6			2																		
		6			4	4		3							7		3	3		2	3.5															
		7			5	5	5								8		4	4		3	4															
31				31	6	6	4	4.5	1	31	31	31	1.5	9		31	5	5				1	31	31												
31.5	1.5	8		31.5	7	8		5.5		31.5	31.5	31.5		10	5		6	6	5	4	4.5	2														
32		9		32	7	8		6	3	32	32	32	2	11	6	31.5	7	7	7		5		31.5	31.5												
32.5		10	6	32.5	9	9		6	5	32.5	32.5			12			8		6	5.5	4															
33	2.5	11		33					6	33	33	32	2.5			32	8		8	7		5	32	32												
	3	12			10	11	11	9		7			32.5		13	7		9	9		6	6														
33.5		7	3.5	11				10	6.5	8	33.5	33.5	33		14		32.5	9	10		8	7	32.5	32.5												
34	3.5	13		34	12	12	12			9	34	34	33.5	3			33		11	10	9	6.5	8	33	33											
					13	13		7	10						15	8		10		10																
34.5	4	14	8	34.5	13	14	14	11	7.5	11	34.5	34.5			16			11	12	11		7	9													
		15			14	15		12	8	12			33.5	3.5		33.5		13	12		7.5	10	33.5	33.5												
35	4.5	16	9	35				15	13	8.5	13	35	35	34		17	9	34	12	14	13	11	8	11	34	34										
35.5	5	17	10	35.5	16			16	14	9	14	35.5	35.5	34.5	4	18	10	34.5	14		14	13	8.5	12	34.5	34.5										
													35	4.5	19		35	15	16	15		9	13	35	35											
36		18	12	36	17			16		16	36	36			11					14		14														
	5.5				18	18	18			17			35.5	5	20	12	35.5	16	17	16	15	9.5	15	35.5	35.5											
	6	19	13				19	17	10	18					21		17		17	16		16														
36.5		20	14	36.5	19	19	20		10.5	19	36.5	36.5			13			18	18		10	17														
37	6.5	21		37				18	11	20	37	37	36		22	14	36	18		17	10.5	18	36	36												
	7	15			20	20	21		11.5	21			36.5	6.5	23	15		19	19		11	19														
37.5		22	16	37.5				22	19	22	37.5	37.5			7	24	16		20	20	20	11.5	20	36.5	36.5											
	7.5				21	21		12.5					37		25	17	37		21	19	12.5		37	37												
	8	24	18	38	22	23	23	21	13.5	24	38	38			7.5	26		21	21	22		22														
					23			22	14	25			37.5		27	18	37.5		22		20		37.5	37.5												
38.5		26	19	38.5	24	24		14.5		38.5	38.5			28	19		22	23	23	21	13	23														
39		27	21	39	24	25		24	15	27	39	39	38	8	29		38	23		24	22	13.5	24	38	38											
39.5		28	22	39.5				26	26	16	29	39.5	39.5			30	20		24	24		14	25													
	9.5	29			26	27	27	16.5	30				38.5					25	26	24	15	27														
		30	23		27	28	28	17	31				39	8.5		22	39	26	26		25	15.5	28	39	39											
40			24	40				29	28	17.5	40	40	39.5		31	23	39.5		27	26	16		39.5	39.5												
40.5	10	31		40.5	28	29		18	32	40.5	40.5			9	32			27	27	28	27	16.5														
	10.5	32			29	30	31	29					40	9.5		24	40		29	29	31	28	17.5													
41			41	30	31	32	30	18.5		41	41	40.5	10.5		26	40.5	30		31	30	33	29	18													
41.5	11.5		28	32																			40.5	40.5												
													41			27																				
																29	41						1.5	18.5	41	41										